



□□

□□□□□□□□□□□□□□□□□□

□□□□□□□□□□□□□□□□

□□□□□□□□□□

- 1000000□□□□□□□□□□□□□□□□

- □□□□□□□□□□5□

□□□□□□CNC□□

□□□□□□□□□□□□GSK□WIS□□

□□□□□□□□

- □□□□□□□□0.5 bar

□□1.1xpn+1□

- □□□□□□1.5xpn+1 bar

- □□□□□□□□+/- 0.2 bar

□□□□□□1000□/□□□□□□□□□□□□

□□□□□□□□□□□□

□□WRAS/KTW/NSF/FDA/ACS□□□□□□□□□□□□□□□□



I 00000000000000000000

II 00

III 00

iv 00

v 000000 GB 0000000000000000 TUV CE ISO 9001 ADWO-2000 TS PED WRC WRA KTW API 6D API609

VI 000000 0000000000000000000000000000000000 /00 /000000000000



Exhibition Photos



□□□□□□□□□□

□□RKSfluid□□20□□□□70□□□□□□□□□□□□□□□□□□□□