

Figure 1 consists of two parts. Part (a) is a photograph of a blue, cast-iron float valve with a long, thin metal stem and a spherical float. Part (b) is a technical cross-section diagram of the valve. It shows the internal components: a float (1) connected to a stem (2) which operates a lever (3) and a valve seat (4). A small circular component (5) is also shown near the float.

-
- The diagram shows a horizontal pipe system. From left to right, it consists of a handwheel valve labeled 'A', a section of pipe labeled 'B' where a hand is shown adjusting a screw, a float valve assembly labeled 'C' with a float arm and a lever, another handwheel valve labeled 'D', and a final section of pipe labeled 'E'. A line connects the float valve assembly to a float ball submerged in a tank of water, labeled 'F'. An arrow below the pipe indicates the direction of flow from left to right.

1. 鋼製 鋼 鋼製 鋼 鋼製;
2. 鋼製 鋼 EN-GJS-500-7 鋼製 鋼;
3. CF8/SUS304 鋼 鋼 鋼製;
4. EPDM 鋼製 鋼 鋼製鋼製;
5. WRAS 鋼製 鋼 鋼製;
6. PN10/16/25

DN	□	□□	□□1	DN	□	□□	□□1
40	230	139	85	250	730	476	205
50	230	139	85	300	850	526	232

65	290	159	95	350	980	585	262
80	310	179	102	400	1100	624	292
100	350	214	112	500	1250	720	360
125	400	278	127	600	1450	835	424
150	480	233	145	800	1850	1110	515
200	600	407	172	1000	2250	1350	630

□□□□□:

1. □□ □□ DN2 mm □ □ □
2. □□□ Zero □ □□□ □□□□ □□□□.
3. □□□ □ □□ □□□□ □□□□ □□□□.
4. 100 □ □□ □□ □ 64bar □□ □□
5. □□ □□(FB), □□□ □□(RB) □ □□□□ □□ □□(ACD) 6. □□ □□ □□□□ □□ □□,
- 6.1 □□ □□ : 1.1 * PN 1 Bar
- 6.2 □□ □□ : 1.5 * PN 1 Bar
- 6.3 □□ □□ □□: 0.2 Bar
7. 1000Hz □□□ □□ □□ □□ □□
8. □□□ □□ □□ □ □□ □□ □ 9. □□ □□ □□ □□ □□



COMPANY INFORMATION



I 廠址：廣東省，江門新會區。

II 主要 CNC 設備，主要用於，主要用於，主要用於。

III 主要用於，主要用於，主要用於。

VI 主要用於，主要用於，主要用於。

V 主要用於：GB，主要用於，主要用於，TUV CE, ISO 9001, ADWO-2000, TS, PED, WRC WRAS, KTW, API 6D, API609.

VI 主要用於：主要用於，主要用於，主要用於，主要用於，主要用於，主要用於，主要用於，主要用於。

COMPANY FACTORY



01

21 years of professional experience

03

Independent research and development team
28 top senior professional researchers

05

100% high level ex-factory inspection

07

2 years quality assurance, repair and replacement

4 factories

02

2 professional testing centers

04

High quality imported materials

06

COMPANY QUALIFICATION



COMPANY EXHIBITION



Partners



Delivery



Payment



FAQ

Q: 如何付款 和 如何 运输?

答: 我们 接受 信用证, 电汇, 支票, 现金 付款。

Q: 如何 运输 和 运输时间 多久 可以 收到?

答: 海运, 空运, 陆运, 运输时间 约 15-30 天。 RKSfluid 提供 各种 运输 服务。 我们 可以 提供 详细 的 运输 方案。

Q: 如何 运输 和 运输时间?

答: RKSfluid 提供 各种 运输 服务 和 40 英尺 集装箱 运输。

Q: 如何 运输?

答: 我们 提供 各种 运输 服务 2~5 天 可以 收到 货物。 我们 可以 提供 详细 的 运输 方案。

问: MOQ

答: 我们 接受 1pc。

Q: 如何 运输 和 运输时间?

答: 我们 提供 100% 的 运输 服务, 约 2 天。 我们 可以 提供 详细 的 运输 方案。

我们 符合 TUV, API, WRAS, CE, ISO 9001 认证。

我们 符合 DIN, ASME, BS EN, JIS, API, AWWA 标准。

Q: 如何 运输 和 运输时间 多久 可以 收到?

答: RKSfluid 20 年 以来 一直 从事 70 年 以来 R&D 服务 和 生产, 我们 可以 提供 详细 的 运输 方案。